

**ARCA 608030**



Sample photo

**Order symbol:** ARCA 608030  
**Product nbr:** 8120029  
**Description:** Cabinet, PC  
**Remarks:** 2-point locking

**EAN:** 6418074085160  
**EI. number:**  
 Finland: 3424064  
 Electric No. 8212095368  
 Denmark:  
 Electric No. Sweden: 2500121

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.

Dimensions:	Length	Width	Height	Accessories:
<b>mm:</b>	600	800	300	MPP ARCA 6080
<b>inch:</b>	23.6	31.5	11.8	MPMP ARCA 8060

Materials:	
<b>Material:</b>	Polycarbonate
<b>Base colour:</b>	RAL 7035 -light grey
<b>Cover colour:</b>	RAL 7035 -light grey
<b>Gasket material:</b>	Polyurethane

Temperatures:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C
<b>Temperature °C (continuous):</b>	-40 ... 80 °C
<b>Temperature °F (short term):</b>	-40 ... 250 °F
<b>Temperature °F (continuous):</b>	-40 ... 175 °F

Accessories:	
MPS ARCA 8060	Mounting plate (730x530x2 mm)

MPP ARCA 6080	Mounting plate perforated (730x530x2 mm - 26x11 mm)
MPMP ARCA 8060	Mounting plate multiperforated (730x530x2 mm - □3.6 mm)
MPX ARCA 8060	Mounting plate (730x530 mm)
IDS ARCA 6080	Inner door set
PMK ARCA 80	Pole mounting kit
RCS ARCA 6080	Rain canopy set
SBK ARCA 60	Support bar kit
SBK ARCA 80	Support bar kit
DSP ARCA LM	Door stopper ARCA, left, midsize, for 5070-8060
DSP ARCA RM	Door stopper ARCA, right, midsize for 5070-8060

Rating:
Ingress Protection (EN 60529): IP66
Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 4, 4X, 12 and 13

**Certificates:**  
SGS Fimko

