

**ARCA 608030S**



Sample photo

**Order symbol:** ARCA 608030S  
**Product nbr:** 8120109  
**Description:** Cabinet, PC  
**Remarks:** Swinghandle

**EAN:** 6418074085221  
**EI. number:**  
**Finland:** 3424068  
**Electric No. Denmark:** 8212095407

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	600	800	300	MPP ARCA 6080	Mounting plate perforated (730x530x2 mm - 26x11 mm)
<b>inch:</b>	23.6	31.5	11.8	MPMP ARCA 8060	Mounting plate multiperforated (730x530x2 mm - □3.6 mm)
Materials:				MPX ARCA 8060	Mounting plate (730x530 mm)
<b>Material:</b>	Polycarbonate			IDS ARCA 6080	Inner door set
<b>Base colour:</b>	RAL 7035 -light grey			PMK ARCA 80	Pole mounting kit
<b>Cover colour:</b>	RAL 7035 -light grey			RCS ARCA 6080	Rain canopy set
<b>Gasket material:</b>	Polyurethane			SBK ARCA 60	Support bar kit
				SBK ARCA 80	Support bar kit
Temperatures:				DSP ARCA LM	Door stopper ARCA, left, midsize, for 5070-8060
<b>Temperature °C (short term):</b>	-40 ... 120 °C			DSP ARCA RM	Door stopper ARCA, right, midsize for 5070-8060
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Rating:	
<b>Temperature °F (short term):</b>	-40 ... 250 °F			Ingress Protection (EN 60529): IP66	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C	
Accessories:				Electrical insulation: Totally insulated	
MPS ARCA 8060	Mounting plate (730x530x2 mm)			Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 94 5VA	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				Certificates:	
				SGS Fimko	

