

ARCA 608030W



Sample photo

Order symbol: ARCA 608030W
Product nbr: 8120149
Description: Cabinet, PC
Remarks: Cover with window, 2-point locking

EAN: 6418074085245
EI. number:
 Finland: 3424072
 Electric No. Denmark: 8212095449
 Electric No. Sweden: 2500155

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	600	800	300	MPP ARCA 6080	Mounting plate perforated (730x530x2 mm - 26x11 mm)
inch:	23.6	31.5	11.8	MPMP ARCA 8060	Mounting plate multiperforated (730x530x2 mm - □3.6 mm)
Materials:				MPX ARCA 8060	Mounting plate (730x530 mm)
Material:	Polycarbonate			IDS ARCA 6080	Inner door set
Base colour:	RAL 7035 -light grey			PMK ARCA 80	Pole mounting kit
Cover colour:	RAL 7035 -light grey			RCS ARCA 6080	Rain canopy set
Gasket material:	Polyurethane			SBK ARCA 60	Support bar kit
				SBK ARCA 80	Support bar kit
Temperatures:				DSP ARCA LM	Door stopper ARCA, left, midsize, for 5070-8060
Temperature °C (short term):	-40 ... 120 °C			DSP ARCA RM	Door stopper ARCA, right, midsize for 5070-8060
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 250 °F			Rating:	
Temperature °F (continuous):	-40 ... 175 °F			Ingress Protection (EN 60529): IP65	
Accessories:				Impact Resistance (EN 62262): IK08	
MPS ARCA 8060	Mounting plate (730x530x2 mm)			Electrical insulation: Totally insulated	
				Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 94 5VA	
				Glow Wire Test (IEC 695-2-1) °C: 960	
Certificates:				SGS Fimko	
				Gost R	

