

ARCA 608030SW



Sample photo

Order symbol: ARCA 608030SW
Product nbr: 8120229
Description: Cabinet, PC
Remarks: Cover with window, Swinghandle

EAN: 6418074085283
EI. number:
Finland: 3424076
Electric No. Denmark: 8212095481

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:	Length	Width	Height	Accessories:
mm:	600	800	300	MPP ARCA 6080
inch:	23.6	31.5	11.8	MPMP ARCA 8060

Materials:	
Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures:	
Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:	
MPS ARCA 8060	Mounting plate (730x530x2 mm)

MPP ARCA 6080	Mounting plate perforated (730x530x2 mm - 26x11 mm)
MPMP ARCA 8060	Mounting plate multiperforated (730x530x2 mm - □3.6 mm)
MPX ARCA 8060	Mounting plate (730x530 mm)
IDS ARCA 6080	Inner door set
PMK ARCA 80	Pole mounting kit
RCS ARCA 6080	Rain canopy set
SBK ARCA 60	Support bar kit
SBK ARCA 80	Support bar kit
DSP ARCA LM	Door stopper ARCA, left, midsize, for 5070-8060
DSP ARCA RM	Door stopper ARCA, right, midsize for 5070-8060

Rating:
Ingress Protection (EN 60529): IP65
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C: 960

Certificates:
SGS Fimko
Gost R

