

**ARCA 507030**



Sample photo

**Order symbol:** ARCA 507030  
**Product nbr:** 8120031  
**Description:** Cabinet, PC  
**Remarks:** 2-point locking

**EAN:** 6418074086006  
**EI. number:**  
 Finland: 3424062  
 Electric No. 8212095384  
 Denmark:  
 Electric No. Sweden: 2500119

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	500	700	300	MPP ARCA 5070	Mounting plate perforated (630x430x2 mm - 26x11 mm)
<b>inch:</b>	19.7	27.6	11.8	MPMP ARCA 7050	Mounting plate multiperforated (630x430x2 mm - □3.6 mm)
Materials:				MPX ARCA 7050	Mounting plate (630x430 mm)
<b>Material:</b>	Polycarbonate			DRS ARCA 507030	DIN rail frame set
<b>Base colour:</b>	RAL 7035 -light grey			IDS ARCA 5070	Inner door set
<b>Cover colour:</b>	RAL 7035 -light grey			PMK ARCA 70	Pole mounting kit
<b>Gasket material:</b>	Polyurethane			RCS ARCA 5070	Rain canopy set
Temperatures:				SBK ARCA 50	Support bar kit
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SBK ARCA 70	Support bar kit
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			DSP ARCA LM	Door stopper ARCA, left, midsize, for 5070-8060
<b>Temperature °F (short term):</b>	-40 ... 250 °F			DSP ARCA RM	Door stopper ARCA, right, midsize for 5070-8060
<b>Temperature °F (continuous):</b>	-40 ... 175 °F				

Accessories:	
MPS ARCA 7050	Mounting plate (630x430x2 mm)

**Rating:**  
 Ingress Protection (EN 60529): IP66  
 Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C  
 Electrical insulation: Totally insulated  
 Halogen free (DIN/VDE 0472, Part 815): 1  
 UV resistance: UL 508  
 Flammability Rating: UL 94 5VA  
 Glow Wire Test (IEC 695-2-1) °C: 960

**Certificates:**  
 SGS Fimko  
 Gost R

