

ARCA 507030S



Sample photo

Order symbol: ARCA 507030S
Product nbr: 8120111
Description: Cabinet, PC
Remarks: Swinghandle

EAN: 6418074086044
EI. number:
Finland: 3424066
Electric No. Denmark: 8212095423

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.

Dimensions:	Length	Width	Height	Accessories:
mm:	500	700	300	MPP ARCA 5070
inch:	19.7	27.6	11.8	MPMP ARCA 7050

Materials:	
Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures:	
Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:	
MPS ARCA 7050	Mounting plate (630x430x2 mm)

MPP ARCA 5070	Mounting plate perforated (630x430x2 mm - 26x11 mm)
MPMP ARCA 7050	Mounting plate multiperforated (630x430x2 mm - □3.6 mm)
MPX ARCA 7050	Mounting plate (630x430 mm)
DRS ARCA 507030	DIN rail frame set
IDS ARCA 5070	Inner door set
PMK ARCA 70	Pole mounting kit
RCS ARCA 5070	Rain canopy set
SBK ARCA 50	Support bar kit
SBK ARCA 70	Support bar kit
DSP ARCA LM	Door stopper ARCA, left, midsize, for 5070-8060
DSP ARCA RM	Door stopper ARCA, right, midsize for 5070-8060

Rating:
Ingress Protection (EN 60529): IP66
Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C: 960

Certificates:
SGS Fimko

