



Sample photo

Order symbol: AR10106CHSC
Product nbr: 8561110
Description: PC Enclosure
Remarks: Hinged opaque screw cover

EAN: 6418074066572
El. number:
Finland:

Including: Hinged screw cover base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

| Dimensions: | Length | Width | Height | Accessories: |
|-------------------------------------|----------------------|-------|--------|---|
| mm: | 254 | 254 | 152 | ABP1010 Painted Steel Back Panel |
| inch: | 10.0 | 10.0 | 6.0 | ALBP1010 Aluminum Back Panel |
| Materials: | | | | ADFP1010 Dead Front Panel w/ screws |
| Material: | Polycarbonate | | | ASP1010 Aluminum Swing Panel |
| Base colour: | RAL 7035 -light grey | | | ASPK1010 Swing Panel Kit incl. Panel |
| Cover screws material: | Stainless steel | | | ASPHK10 Swing Panel Kit w/o Panel |
| Cover colour: | RAL 7035 -light grey | | | AMFL10 10" Mounting Flange Set |
| Gasket material: | Polyurethane | | | |
| Temperatures: | | | | Rating: |
| Temperature °C (short term): | -40 ... 140 °C | | | Ingress Protection (EN 60529): IP66/IP67 |
| Temperature °C (continuous): | -40 ... 80 °C | | | Impact Resistance (EN 62262): IK09 |
| Temperature °F (short term): | -40 ... 284 °F | | | Electrical insulation: Totally insulated |
| Temperature °F (continuous): | -40 ... 175 °F | | | Halogen free (DIN/VDE 0472, Part 815): 0 |
| Accessories: | | | | UV resistance: UL 508 |
| APBP1010 | PVC Back Panel | | | Flammability Rating: UL 508 |
| | | | | Glow Wire Test (IEC 695-2-1) °C: 960 |
| | | | | NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13 |

