



Sample photo

Order symbol: AR181610CHSC
Product nbr: 8561068
Description: PC Enclosure
Remarks: Hinged opaque screw cover

EAN: 6418074066657
EI. number:
Finland:

Including: Hinged screw cover base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	457	406	254	ALBP1816	Aluminum Back Panel
inch:	18.0	16.0	10.0	ADFP1816	Dead Front Panel w/ screws
Materials:				ASP1816	Aluminum Swing Panel
Material:	Polycarbonate			APSPK1816 Plastic	Swing Panel Kit incl. Panel
Base colour:	RAL 7035 -light grey			ASPK1816	Swing Panel Kit incl. Panel
Cover screws material:	Stainless steel			AMFL16	16" Mounting Flange Set
Cover colour:	RAL 7035 -light grey			Rating:	
Gasket material:	Polyurethane			Ingress Protection (EN 60529): IP66/IP67	
Temperatures:				Impact Resistance (EN 62262): IK09	
Temperature °C (short term):	-40 ... 140 °C			Electrical insulation: Totally insulated	
Temperature °C (continuous):	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 0	
Temperature °F (short term):	-40 ... 284 °F			UV resistance: UL 508	
Temperature °F (continuous):	-40 ... 175 °F			Flammability Rating: UL 508	
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960	
ABP1816	Painted Steel Back Panel			NEMA Class: NEMA 4, 4X, 12 and 13	

