

MNX PC 150/100 HT



Sample photo

Order symbol: PC 150/100 HT
Product nbr: 6011915
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074022431
EI. number:
 Finland: 3420465
 Electric No. Denmark: 8212022483
 Electric No. Italy: 7352100
 Electric No. Sweden: 2535657

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	180	130	100	MIN 10	DIN-15 Mounting rail
inch:	7.1	5.1	3.9	MIN 15	DIN-15 Mounting rail
				MIV 10	DIN-35 Mounting rail
				MIV 15	DIN-35 Mounting rail
				FP A 150/180	Front plate (Aluminium)
				HFP 180	Front plate hinge series
				FP 22046	Wall fastening lug (4 pcs)
Materials:				Rating:	
Material:	Polycarbonate			Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK08	
Cover screws material:	Polyamide			Electrical insulation: Totally insulated	
Cover colour:	Smoked grey			Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Black			UV resistance: UL 508	
Gasket material:	TPE			Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 4, 4X, 6	
Temperatures:				Certificates:	
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko	
Temperature °C (continuous):	-40 ... 80 °C			Gost R	
Temperature °F (short term):	-40 ... 250 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
MIV 150	Mounting plate (Galvanized steel)				

