

**ARCA 403021**

**Order symbol:** ARCA 403021  
**Product nbr:** 8120007  
**Description:** Cabinet, PC  
**Remarks:** 2-point locking

**EAN:** 6418074079183  
**EI. number:**  
 Finland: 3423054  
 Electric No. 8212091058  
 Denmark:  
 Electric No. Sweden: 2500114



Sample photo

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:	Length	Width	Height	Rating:
mm:	400	300	210	Ingress Protection (EN 60529): IP66
inch:	15.7	11.8	8.3	Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C
<b>Materials:</b>				Electrical insulation: Totally insulated
<b>Material:</b>	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
<b>Base colour:</b>	RAL 7035 -light grey			UV resistance: UL 508
<b>Cover colour:</b>	RAL 7035 -light grey			Flammability Rating: UL 94 5VA
<b>Gasket material:</b>	Polyurethane			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Temperatures:</b>				<b>Certificates:</b>
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SGS Fimko
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Gost R
<b>Temperature °F (short term):</b>	-40 ... 250 °F			
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			

