

ARCA 504021

Order symbol: ARCA 504021
Product nbr: 8120011
Description: Cabinet, PC
Remarks: 2-point locking

EAN: 6418074079220
EI. number:
 Finland: 3423099
 Electric No. 8212091090
 Denmark:
 Electric No. Sweden: 2500116



Sample photo

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. Door guide included.

Dimensions:	Length	Width	Height	Accessories:	
mm:	500	400	210	MPP ARCA 5040	Mounting plate perforated (450x350x2 mm - 26x11 mm)
inch:	19.7	15.7	8.3	MPMP ARCA 5040	Mounting plate multiperforated (450x350x2 mm - □3.6 mm)
Materials:				MPX ARCA 5040	Mounting plate (450x350 mm)
Material:	Polycarbonate			DRS ARCA 504015	DIN rail frame set
Base colour:	RAL 7035 -light grey			DRS ARCA 504021	DIN rail frame set
Cover colour:	RAL 7035 -light grey			IDS ARCA 5040	Inner door set
Gasket material:	Polyurethane			PMK ARCA 40	Pole mounting kit
Temperatures:				RCS ARCA 5040	Rain canopy set
Temperature °C (short term):	-40 ... 120 °C			SBK ARCA 40	Support bar kit
Temperature °C (continuous):	-40 ... 80 °C			SBK ARCA 50	Support bar kit
Temperature °F (short term):	-40 ... 250 °F			DSP ARCA VLS	Door stopper ARCA, vertical, left, small
Temperature °F (continuous):	-40 ... 175 °F			DSP ARCA VRS	Door stopper ARCA, vertical, right, small

Accessories:	
MPS ARCA 5040	Mounting plate (450x350x2 mm)

Rating:
 Ingress Protection (EN 60529): IP66
 Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 94 5VA
 Glow Wire Test (IEC 695-2-1) °C: 960
 NEMA Class: NEMA 4, 4X, 12 and 13

Certificates:
 SGS Fimko

