

ARCA 203015



Sample photo

Order symbol: ARCA 203015
Product nbr: 8120020
Description: Cabinet, PC
Remarks: 1-point locking

EAN: 6418074079312
EI. number:
 Finland: 3423117
 Electric No. 8212091184
 Denmark:
 Electric No. Sweden: 2500109

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	200	300	150	MPP ARCA 2030	Mounting plate perforated (250x150x2 mm - 26x11 mm)
inch:	7.9	11.8	5.9	MPMP ARCA 3020	Mounting plate multiperforated (250x150x2 mm - □3.6 mm)
Materials:				MPX ARCA 3020	Mounting plate (250x150 mm)
Material:	Polycarbonate			DRS ARCA 203015	DIN rail frame set
Base colour:	RAL 7035 -light grey			IDS ARCA 2030	Inner door set
Cover colour:	RAL 7035 -light grey			PMK ARCA 30	Pole mounting kit
Gasket material:	Polyurethane			RCS ARCA 2030	Rain canopy set
Temperatures:				SBK ARCA 20	Support bar kit
Temperature °C (short term):	-40 ... 120 °C			SBK ARCA 30	Support bar kit
Temperature °C (continuous):	-40 ... 80 °C			Rating:	
Temperature °F (short term):	-40 ... 250 °F			Ingress Protection (EN 60529): IP66	
Temperature °F (continuous):	-40 ... 175 °F			Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C	
Accessories:				Electrical insulation: Totally insulated	
MPS ARCA 3020	Mounting plate (250x150x2 mm)			Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 94 5VA	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				Certificates:	
				SGS Fimko	
				Gost R	

