

ARCA 304021



Sample photo

Order symbol: ARCA 304021
Product nbr: 8120023
Description: Cabinet, PC
Remarks: 2-point locking

EAN: 6418074079343
EI. number:
 Finland: 3423120
 Electric No. 8212091210
 Denmark:
 Electric No. Sweden: 2500113

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:	Length	Width	Height	Rating:
mm:	300	400	210	Ingress Protection (EN 60529): IP66
inch:	11.8	15.7	8.3	Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C
Materials:				Electrical insulation: Totally insulated
Material:	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7035 -light grey			UV resistance: UL 508
Cover colour:	RAL 7035 -light grey			Flammability Rating: UL 94 5VA
Gasket material:	Polyurethane			Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:				Certificates:
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko
Temperature °C (continuous):	-40 ... 80 °C			Gost R
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			

