

ARCA 406021W



Sample photo

Order symbol: ARCA 406021W
Product nbr: 8120146
Description: Cabinet, PC
Remarks: Cover with window, 2-point locking

EAN: 6418074080172
EI. number:
 Finland: 3423225
 Electric No. Denmark: 8212092028
 Electric No. Sweden: 2500145

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	400	600	210	MPP ARCA 4060	Mounting plate perforated (550x350x2 mm - 26x11 mm)
inch:	15.7	23.6	8.3	MPMP ARCA 6040	Mounting plate multiperforated (550x350x2 mm - □3.6 mm)
Materials:				MPX ARCA 6040	Mounting plate (550x350 mm)
Material:	Polycarbonate			DRS ARCA 406021	DIN rail frame set
Base colour:	RAL 7035 -light grey			IDS ARCA 4060	Inner door set
Cover colour:	RAL 7035 -light grey			PMK ARCA 60	Pole mounting kit
Gasket material:	Polyurethane			RCS ARCA 4060	Rain canopy set
Temperatures:				SBK ARCA 40	Support bar kit
Temperature °C (short term):	-40 ... 120 °C			SBK ARCA 60	Support bar kit
Temperature °C (continuous):	-40 ... 80 °C			DSP ARCA HLS	Door stopper ARCA, horizontal, left, small
Temperature °F (short term):	-40 ... 250 °F			DSP ARCA HRS	Door stopper ARCA, horizontal, right, small
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:				Rating:	
MPS ARCA 6040	Mounting plate (550x350x2 mm)			Ingress Protection (EN 60529): IP65	
				Impact Resistance (EN 62262): IK08	
				Electrical insulation: Totally insulated	
				Halogen free (DIN/VDE 0472, Part 815): 1	
				UV resistance: UL 508	
				Flammability Rating: UL 94 5VA	
				Glow Wire Test (IEC 695-2-1) °C: 960	

Certificates:

SGS Fimko
Gost R

