

ARCA 405021SW



Sample photo

Order symbol: ARCA 405021SW
Product nbr: 8120225
Description: Cabinet, PC
Remarks: Cover with window, Swinghandle

EAN: 6418074080684
EI. number:
 Finland: 3423289
 Electric No. 8212092536
 Denmark:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:	Length	Width	Height	Accessories:	
mm:	400	500	210	MPP ARCA 4050	Mounting plate perforated (450x350x2 mm - 26x11 mm)
inch:	15.7	19.7	8.3	MPMP ARCA 5040	Mounting plate multiperforated (450x350x2 mm - □3.6 mm)
Materials:				MPX ARCA 5040	Mounting plate (450x350 mm)
Material:	Polycarbonate			DRS ARCA 405021	DIN rail frame set
Base colour:	RAL 7035 -light grey			IDS ARCA 4050	Inner door set
Cover colour:	RAL 7035 -light grey			PMK ARCA 50	Pole mounting kit
Gasket material:	Polyurethane			RCS ARCA 4050	Rain canopy set
Temperatures:				SBK ARCA 40	Support bar kit
Temperature °C (short term):	-40 ... 120 °C			SBK ARCA 50	Support bar kit
Temperature °C (continuous):	-40 ... 80 °C			DSP ARCA HLS	Door stopper ARCA, horizontal, left, small
Temperature °F (short term):	-40 ... 250 °F			DSP ARCA HRS	Door stopper ARCA, horizontal, right, small
Temperature °F (continuous):	-40 ... 175 °F				

Accessories:	
MPS ARCA 5040	Mounting plate (450x350x2 mm)

Rating:
 Ingress Protection (EN 60529): IP65
 Impact Resistance (EN 62262): IK08
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 94 5VA
 Glow Wire Test (IEC 695-2-1) °C: 960

Certificates:
 SGS Fimko
 Gost R

