

**ARCA 406021SW**



Sample photo

**Order symbol:** ARCA 406021SW  
**Product nbr:** 8120226  
**Description:** Cabinet, PC  
**Remarks:** Cover with window, Swinghandle

**EAN:** 6418074080691  
**EI. number:**  
 Finland: 3423290  
 Electric No. 8212092549  
 Denmark:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	400	600	210	MPP ARCA 4060	Mounting plate perforated (550x350x2 mm - 26x11 mm)
inch:	15.7	23.6	8.3	MPMP ARCA 6040	Mounting plate multiperforated (550x350x2 mm - □3.6 mm)
Materials:				MPX ARCA 6040	Mounting plate (550x350 mm)
<b>Material:</b>	Polycarbonate			DRS ARCA 406021	DIN rail frame set
<b>Base colour:</b>	RAL 7035 -light grey			IDS ARCA 4060	Inner door set
<b>Cover colour:</b>	RAL 7035 -light grey			PMK ARCA 60	Pole mounting kit
<b>Gasket material:</b>	Polyurethane			RCS ARCA 4060	Rain canopy set
Temperatures:				SBK ARCA 40	Support bar kit
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SBK ARCA 60	Support bar kit
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			DSP ARCA HLS	Door stopper ARCA, horizontal, left, small
<b>Temperature °F (short term):</b>	-40 ... 250 °F			DSP ARCA HRS	Door stopper ARCA, horizontal, right, small
<b>Temperature °F (continuous):</b>	-40 ... 175 °F				

Accessories:	
MPS ARCA 6040	Mounting plate (550x350x2 mm)

**Rating:**  
 Ingress Protection (EN 60529): IP65  
 Impact Resistance (EN 62262): IK08  
 Electrical insulation: Totally insulated  
 Halogen free (DIN/VDE 0472, Part 815): 1  
 UV resistance: UL 508  
 Flammability Rating: UL 94 5VA  
 Glow Wire Test (IEC 695-2-1) °C: 960

**Certificates:**  
 SGS Fimko  
 Gost R

